

Driver

- HPLS-36AD3500
- HPLS-36DD75500
- HPLS-36DD18B
- HPLS-36APL750

- HPLS-30AD3500
- HPLS-30DD7500
- HPLS-30DD7500-P2
- HPLS-30DD7500-P3
- HPLS-30DD7500-2C
- HPLS-30DD7500-4C

- HPLS-45AD3500
- HPLS-45APXXX-3DEXT
- HPLS-45-RXXX-3DEXT

Interchangeable LED UV/VIS/NIR



HPLS-36RS1 LED Socket

HPLS-26RS2 LED Socket

Collimating / Focusing Optic



OH36-24X11

1 inch Filter

OH36-38X17.5

OH26-30X15 Square Collimator

Ø19.0X15-WIN Window

OH26-25X0.1NA

OH26-25X0.5NA

OH26-(8+8)DEG Beam Steering Wedges

Additional Output Options

PDP-36-FL Photodiode Option

FL-25X.5 Fiber Launcher

FA-Adapter



Light Guide

Fiber Bundle

Fiber

POF

OH36-24X11-C/CS

OH36-CU36-MC Adapter


OH36-CU36 Beam Combiner 2 input ports

OH36-CU36-MC Microscope Adapter

2 Wavelength Output

OH36-CU36 Beam Combiner 2 input ports

3 Wavelength Output



HPLS-36AD3500 available with dual input (analog and short pulse digital simultaneously)

Fixed Pulse Width configurations available where trigger fires preset pulse width.